

1.0" slot width	1 slot	Airflow, cfm	25	40	55	70	85	100	115
		static pressure	0.028	0.072	0.136	0.221	0.325	0.450	0.596
		NC (noise criteria)	<10	+16	26	33	39	44	49
		Throw	5-8-14	9-13-18	12-15-21	14-17-24	15-19-27	17-20-29	18-22-31
	2 slot	Airflow, cfm	50	75	100	125	150	175	200
		Static pressure	0.028	0.063	0.113	0.176	0.253	0.345	0.450
		NC (noise criteria)	<10	17	26	33	39	44	48
		Throw	7-11-20	11-17-25	15-20-29	19-23-32	20-25-35	22-27-38	23-29-41
1.5" slot width	1 slot	Airflow, cfm	30	45	60	75	90	105	120
		Static pressure	0.032	0.073	0.130	0.203	0.292	0.398	0.520
		NC (noise criteria)	<10	14	24	31	37	42	48
		Throw	6-10-16	10-14-19	13-16-22	14-18-25	16-19-27	17-21-29	18-22-32
	2 slot	Airflow, cfm	60	85	110	135	160	185	210
		Static pressure	0.032	0.065	0.109	0.164	0.231	0.309	0.398
		NC (noise criteria)	<10	16	24	31	36	41	45
		Throw	9-14-22	13-19-27	17-21-30	19-24-33	21-26-36	23-28-39	24-29-42

2.0" slot width	1 slot	Airflow, cfm	30	50	70	90	110	130	150
		Static pressure	0.020	0.057	0.111	0.184	0.274	0.383	0.510
		NC (noise criteria)	<10	11	22	30	36	41	46
		Throw	5-9-16	9-14-20	13-17-24	16-19-27	17-21-30	19-23-33	20-25-35
	2 slot	Airflow, cfm	60	95	130	165	200	235	270
		Static pressure	0.020	0.051	0.096	0.154	0.227	0.313	0.413
		NC (noise criteria)	<10	12	22	30	36	41	46
		Throw	7-12-22	13-19-28	17-23-33	21-26-37	23-29-41	25-31-44	27-33-47
2.5" slot width	1 slot	Airflow, cfm	30	55	80	105	130	155	180
		Static pressure	0.012	0.041	0.088	0.151	0.232	0.329	0.444
		NC (noise criteria)	<10	11	23	31	38	43	48
		Throw	4-8-16	10-15-21	14-18-26	17-21-29	19-23-33	21-25-36	22-27-39
	2 slot	Airflow, cfm	60	105	150	195	240	285	330
		Static pressure	0.012	0.038	0.077	0.130	0.197	.0278	0.373
		NC (noise criteria)	<10	13	24	32	38	44	48
		Throw	6-11-22	13-20-29	19-25-35	23-28-40	26-32-45	28-34-49	30-37-52

3.0" slot width	1 slot	Airflow, cfm	30	60	90	120	150	180	210
		Static pressure	0.011	0.044	0.100	0.177	0.277	0.399	0.543
		NC (noise criteria)	<10	<10	18	27	34	40	45
		Throw	3-7-15	10-15-22	15-19-27	18-22-32	20-25-35	22-27-39	24-29-42
	2 slot	Airflow, cfm	60	120	180	240	300	360	420
		Static pressure	0.011	0.044	0.100	0.177	0.277	0.399	0.543
		NC (noise criteria)	<10	<10	21	30	37	43	48
		Throw	5-10-21	14-21-32	21-27-39	26-32-45	29-35-50	32-39-55	34-42-59